

Portable Cabinet


- just the thing for your off-site visits




SIMPLE TO SET-UP



1. POSITION THE BASE



2. UNFOLD THE SIDES



3. PLACE ON THE TOP



VeriVide
See in Truth



- Assemble in Seconds.
- Supplied with 5 Light Sources.
- Package weight of only 12 kgs.

VeriVide's Portable Cabinet . . . Ideal for off-site visits

The Portable version of our CAC range of colour assessment cabinets is ideal for off-site visits to customers and suppliers and with a package weight of around 12 kgs it can be easily carried.

It is very easy to assemble - it just slots together and it comes with its own carry case.

The CAC Portable Cabinet is supplied with 5 Light Sources , which typically are:

- **D65** VeriVide's 'Artificial Daylight',
- A **UV** - Ultraviolet light - used to detect the presence of Optical Brightening Agents and/or Fluorescent dyes.
- **Tungsten 'F'** - required by BS 950: part 1 (1967) as a test for metamerism
- 2 Point of Sale or alternative fluorescent Lamps, selected from the following **840P15, 830, Cool White, D50 or D75**

You can specify the light sources you need, from the choice of lamps available for this product but the specification above is the maximum allowed for the CAC Portable.

Dimensions (mm)	width	height	depth
Overall	675	420	330
Viewing	635	280	280
Closed (e.g. in Carrying Bag)	690	340	160

Package weight 12 kilos.

Please note lamp options 'A' and 'H' are not available for the portable option neither are dimmable options.

Please state required Voltage when ordering. The internal colour is Munsell N5 but if you have a need for an alternative internal colour such as Munsell N7 we can accommodate your requirements.

To find out more please ring +44 (0)116 284 7790 or email enquiries@verivide.com

www.verivide.com